

The Original Ultrasonic Brass Instrument Cleaner

....cleans in only 2 to 4 minutes

Why use the ultrasonic cleaning process?

- Environmentally friendly
- Replaces harmful acids and chemicals
- Prolongs life of instruments
- Cleans inside and out
- Cleans all types and sizes of instruments
- Horn flush accessory for large debris removal
- Stainless steel construction
- Portable design with locking casters



Repair shops, manufacturers, universities and school districts world wide agree that UPC cleaners deliver expected results - clean instruments in less time without hazardous chemicals.



A PROUD SUPPORTER OF NAPBIRT


GENERATOR CERTIFICATIONS



WWW.UPCORP.COM

	SOPRANO	TENOR	BASS
Capacity	9 Gallon / 34 Liter	39 Gallon / 148 Liter	90 Gallon / 340 Liter
Internal Dimensions	8"W x 22"L x 12"D (203mm x 559mm x 304mm)	18"W x 32"L x 16"D (457mm x 813mm x 406mm)	22"W x 48"L x 20"D (559mm x 1219mm x 508mm)
External Dimensions	18"W x 26"L x 17"D (457mm x 660mm x 432mm)	23.5"W x 40.25"L x 39.25"D (597mm x 1022mm x 997mm)	26"W x 60.5"L x 42.5"D (660mm x 1537mm x 1080mm)
Ultrasonic Power (Avg/Peak)	500 watts / 1000 watts	1000 watts / 2000 watts	1500 watts / 3000 watts
Thermostatically Controlled Heat	500 watts	1000 watts	2000 watts
Input Voltage	110-120 VAC 50/60 Hz	220-240 VAC 50/60Hz	220-240 VAC 50/60Hz
Approx. Shipping Weight	115 lbs / 52 kg	385 lbs / 175 kg	550 lbs / 250 kg

Ultrasonic Power Corporation....more POWER to clean.



ULTRASONIC POWER CORPORATION

239 E. Stephenson Street . Freeport, IL USA 61032
815-235-6020 . 800-575-0168 . FAX 815-232-2150

WWW.UPCORP.COM . sonic@upcorp.com